



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH227NRK 800A/2P HD Fusible Safety Switch W/Neut 240V Nema

Eaton Corp

Catalog Number	DH227NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, Enhanced Visible Blade, 800 A, Nema 3R, Painted Galvanized Steel, Class L, Two-Pole, Three-Wire, 240 V, Max HP: 100, 250 HP (3PH @ STD Fuse/Time Delay), (4)#1/0-(4)750 Kcmil Al
Weight per unit	175.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

### Features

amperage rating	800
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	240V

### Dimensions and Weight

Depth	65
Height	13
Width	27

### Descriptions

Description	800A/2P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH227NRK 800A/2P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 800 A, NEMA 3R, Painted galvanized steel, Class L, Two-pole, Three-wire, 240 V, Max Hp: 100, 250 hp (3PH @ Std fuse/time delay), (4)#1/0-(4)750 kcmil Al
Product Type	800A/2P HD FSBL Sfty SW W/Neut 240V N3R
Special Features	Enhanced visible blade

### Manufacturer Information

Brand	Eaton
GTIN	00782113589671
Manufacturers Part Number	DH227NRK
UPC	782113589671



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

## Packaging

Carton 1

Weight Per each 175

## Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier