



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH367URK 800A/3P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH367URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 800A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 500 At 480 Vac TD 3 PH, 500 At 600 Vac TD 3 PH
Weight per unit	158.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	800A
dimensions	14.0700 IN X 26.3700 IN X 55.8200 IN
Material	Painted galvanized steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

Dimensions and Weight

Depth	14.0700
Height	55.8200
Width	26.3700

Descriptions

Description	800A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH367URK 800A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 800A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 500 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph
Product Type	800A/3P HD NF Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113589756
Manufacturers Part Number	DH367URK
UPC	782113589756



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Non-Fusible Safety Switch

Packaging

Carton 1

Weight Per each 158

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating Nema 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier