



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DG132011FBC21C DG1 230V FR1 N1 3HP 11A CT N/A VT W/ BC

Eaton Corp

Catalog Number	DG132011FBC21C
Manufacturer	Eaton Corp
Description	Eaton Powerxl DG1 Variable Frequency Drive, 208-240V Input 2.2 KW 3 HP CT 3PH 50/60 HZ 11A Output IP21/Type 1 FR1 LCD Internal Emc Filter and DC Choke Ethernet, RS-485, Bacnet MS/TP, Modbus TCP and Rtu Ports 2 Exp Slots Brake Chopper
Weight per unit	17.0 (lbs/each)
Product Category	Ac Drives

Features

display	LCD graphical
Input Voltage	230 V, 208-240 V(-15%, +10%)
keypad	Included

Dimensions and Weight

Depth	17.5
Height	13
Width	9

Descriptions

Description	DG1 230V FR1 N1 3HP 11A CT N/A VT W/ BC
extra long description	ETN DG1-32011FB-C21C DG1,230V FR1,N
Features	Demand more flexibility. Eaton's PowerXL DG1 general purpose, variable frequency drives are engineered for today's demanding commercial and industrial applications. With an industry leading energy efficiency algorithm, high short-circuit current rating and robust design, the DG1 offers customers increased efficiency, safety and reliability.
Long Description	Eaton PowerXL DG1 variable frequency drive, 208-240V input 2.2 kW 3 Hp CT 3PH 50/60 Hz 11A output IP21/type 1 FR1 LCD Internal EMC filter and DC choke EtherNet, RS-485, BACnet MS/TP, Modbus TCP and RTU ports 2 exp slots Brake chopper
Product Type	DG1, 230V FR1, N1, 3HP, 11A CT, BC
Special Features	Coated board

Manufacturer Information

Brand	Eaton
GTIN	00786685886046
Manufacturers Part Number	DG1-32011FB-C21C
UPC	786685886046



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DRIVES

Type Variable Frequency Drive

Packaging

Carton 1

Weight Per each 17

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

Enclosure IP21/type 1 enclosure

standard UL 508C,EN ISO 13849-1,IEC 61508,UL Listed,EN 62061,cUL
Listed,RoHS Compliant,CE Marked,GoST-R,C-Tick Compliant