



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH368URK 1200A/3P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH368URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 1200A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire
Weight per unit	475.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

### Features

amperage rating	1200A
dimensions	17.1200 IN X 43.1200 IN X 70.9700 IN
Material	Painted galvanized steel
media	Yes
Poles	Three-pole
Voltage Rating	600 V

### Dimensions and Weight

Depth	17.1200
Height	70.9700
Width	43.1200

### Descriptions

Description	1200A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH368URK 1200A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 1200A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire
Product Type	1200A/3P HD NF Sfty SW 600V N3R

### Manufacturer Information

Brand	Eaton
GTIN	00782114313077
Manufacturers Part Number	DH368URK
UPC	782114313077

### Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 1

Weight Per each ..... 475

## Uses, Certifications, and Standards

Application ..... Commercial / Institutional Buildings / Structures - Power  
Distribution and Controls

nema rating ..... Nema 3R

standard ..... UL Listed, NEC 230.62 (C) Compliant Barrier