



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DT363URK 100A/3P HD NF Double Throw Switch 600V Nema 3R *Eaton Corp*

Catalog Number	DT363URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Double-Throw Non-Fused Safety Switch, 100 A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 600 Vac, 250 VDC
Weight per unit	34.0 (lbs/each)
Product Category	Non-Fusible Double Throw Safet

Features

amperage rating	100
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 VAC, 250 VDC

Dimensions and Weight

Depth	11.19
Height	25.02
Width	11.95

Descriptions

Description	100A/3P HD NF DOUBLE THROW SWITCH 600V NEMA 3R
extra long description	ETN DT363URK 100A/3P HD NF DT Sw 60
Features	Eaton's double-throw safety switches include two interlocked switches with a common connection used to transfer service from a normal power source to an alternate source, or to switch from one load circuit to another. The interlock ensures both switches cannot be closed at the same time, preventing them from being operated in parallel. Additionally, double-throw safety switches are available in general duty and heavy duty as well as quick-connect options.
Long Description	Eaton Heavy duty double-throw non-fused safety switch, 100 A, NEMA 3R, Painted galvanized steel, Non-fusible, Three-pole, Three-wire, 600 Vac, 250 Vdc
Product Type	100A/3P HD NF DT SW 600V N3R



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113426426
Manufacturers Part Number	DT363URK
UPC	782113426426

Taxonomies, Classifications, and Categories

Category Description	DOUBLE THROW SWITCHES (DT Series)
Type	Double-throw non-fused safety switch

Packaging

Carton	1
Weight Per each	34

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
standard	UL Listed