



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DV18250MBCY 18-22AWG Red Insld ML Tab DSCNCT Panduit Corporation

|                  |   |
|------------------|---|
| Catalog Number   | DV18250MBCY   |
| Manufacturer     | Panduit Corporation   |
| Description      | The Vibration Resistant Male Disconnect Is Made Of Copper and Is Nickel-Plated. It Is Barrel Insulated In Red Vinyl Housing. It Has A Tab Size Of 0.250 X 0.032" (6.3 X 0.8 MM) and Supports A Wire Range Of 22-18 Awg (0.5-1.0 MM <sup>2</sup> ). It Is 0.98" (24.9 MM) Long and 0.25" (6.4 MM) Wide. The Disconnect Has A Funnel Entry Barrel Configuration and A Butted Seam Barrel. It Comes In Bottles Of 100. |
| Weight per unit  | 0.3100 (lbs/each)   |
| Product Category | Small Terminals & Connectors  |

### Features

|                |              |
|----------------|--------------|
| connection     | Funnel Entry |
| insulation     | Vinyl        |
| Material       | Copper       |
| Voltage Rating | 600          |
| Wire Size      | #18          |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Color  | Red           |
| Finish | Nickel Plated |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 18-22AWG RED INSLTD ML TAB DSCNCT   |
| extra long description | PAN DV18-250MB-CY Pan-Term® DV18-25   |
| Long Description       | The vibration resistant male disconnect is made of copper and is nickel-plated. It is barrel insulated in red vinyl housing. It has a tab size of 0.250 x 0.032" (6.3 x 0.8 mm) and supports a wire range of 22-18 AWG (0.5-1.0 mm <sup>2</sup> ). It is 0.98" (24.9 mm) long and 0.25" (6.4 mm) wide. The disconnect has a funnel entry barrel configuration and a butted seam barrel. It comes in bottles of 100. |
| Product Type           | Pan-Term® DV18-250MB-Cy Loose Piece Disconnect  |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Panduit®       |
| GTIN                      | 00074983685622 |
| Manufacturers Part Number | DV18-250MB-CY  |
| UPC                       | 074983685622   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |            |
|----------------------|------------|
| Category Description | TERMINALS  |
| Type                 | Disconnect |

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 100  |
| Weight Per each | 0.31 |

## Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Mounting           | 1932-09-01  |
| standard           | CSA Certified LR31212, C22.2 No.153;UL 310 Listed, UL Listed<br>20H3 E78522 |
| Temperature Rating | 221 Degrees Fahrenheit (105 Degrees Celsius)                                |