



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVELV300PWH Diva 300W Electronic Low Voltage SP White

Lutron

| | |
|------------------|--|
| Catalog Number | DVELV300PWH |
| Manufacturer | Lutron |
| Description | Dimmable Bulb, Claro Switch/Mechanical Switch, 120 V, 300 W, 60 HZ, Incandescent Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +0 °C Operating Temperature, +40 °C Operating Temperature, 1 Yr Warranty, 0.3 LB/Ea |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|---------------|
| actuator | Paddle Switch |
| connection | Wire Leads |
| Connection Type | Wire Leads |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Voltage Rating | 120 |
| Wattage | 300 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Gloss |
|--------|-------|

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|

Descriptions

| | |
|------------------------|--|
| Description | DIVA 300W ELECTRONIC LOW VOLTAGE SP WHITE |
| extra long description | LUT DVELV-300P-WH DIVA ELV 300 WATT |
| Special Features | Controls 300 W electronic low-voltage loads. Paddle turns on/off. Slide up to brighten, down to dim. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00027557748292 |
| UPC | 027557748292 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Dimmer, single-pole |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.3 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-----------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA, NOM |