



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVSTVLA Diva DV 8A 0-10V 3WAY Light Almond

Lutron

| | |
|------------------|---|
| Catalog Number | DVSTVLA |
| Manufacturer | Lutron |
| Description | Diva Dimmer - Gloss Finish, Fluorescent or Led Dimming With 0-10V Ballasts and Drivers, Single-Pole/3-Way, 120-277V/50MA/8A In Light Almond |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|---------------|
| actuator | Paddle Switch |
| amperage rating | 8 |
| connection | Wire Leads |
| Connection Type | Wire Leads |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Switch Type | Paddle Switch |
| Voltage Rating | 120 to 277 |
| Wattage | 2216 |

Material, Color, and Finish

| | |
|--------|--------------|
| Color | Light Almond |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | DIVA DV 8A 0-10V 3WAY LIGHT ALMOND |
| extra long description | LUT DVSTV-LA DIVA 0-10 W/SWITCHING |
| Features | The Diva 0-10V dimmer switch is a simple solution is designed to match existing design style switches and accessories. Easily turn the lights on and off with a paddle switch, and use the slide control to adjust the lights to the perfect level. The new Diva 0 - 10-Volt dimmerswitch is a 0-10 VDC dimmer with 3-way functionality for 3rd party 0-10-Volt fixtures (LED and fluorescent), no separate power pack required. Coordinating wall plate sold separately. |
| Long Description | Diva Dimmer - Gloss Finish, Fluorescent or LED Dimming with 0-10V Ballasts and Drivers, Single-pole/3-way, 120-277V/50mA/8A in light almond |
| Product Type | Diva 0-10 W/Switching Box Light Almond |
| Special Features | Controls 0-10 V LED or fluorescent fixture loads, 50 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276099615 |
| Manufacturers Part Number | DVSTV-LA |
| UPC | 784276099615 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Dimmer, 3-way/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 0.26 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | Indoor use only |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA |