



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005



E22PB2 PB Flush BKBZ R *Eaton Corp*

Catalog Number	E22PB2
Manufacturer	Eaton Corp
Description	Eaton, Non-Metallic Heavy-Duty Pushbutton, Red, Plastic Actuator, Black Bezel, 1NO, Non-Illuminated, Flush Mounting, Nema 3, 3R, 4, 4X, 12, 13, Momentary, 22.5 MM, Flush Pushbutton, E22 Series
Weight per unit	0.0800 (lbs/each)
Product Category	Push Button Components

Features

action	Red
actuator	Flush
Contact Configuration	1 NO

Dimensions and Weight

Depth	2
Height	1.5
Size	22.5 mm
Width	1.5

Descriptions

Description	PB FLUSH BKBZ R
extra long description	ETN E22PB2 PB FLUSH BKBZ R
Features	Eaton's 22.5 mm industrial heavy-duty pushbutton line offers a wide array of functional, smartly styled illuminated and non-illuminated pushbuttons, selector switches, push-pulls, action and twist-to- release operators. The complete line also includes transformer, full voltage, resistor, LED or neon light units.
Long Description	Eaton, Non-metallic Heavy-Duty Pushbutton,Red,Plastic Actuator,Black bezel,1NO,Non-illuminated,Flush mounting,NEMA 3, 3R, 4, 4X, 12, 13,Momentary,22.5 mm,Flush Pushbutton,E22 Series
Product Type	PB Flush BKBZ R



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 South Persimmon Street
77375-6855, TX Tomball
Phone: 281-357-5300
Fax: 281-357-5005

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113469041
Manufacturers Part Number	E22PB2
Model	Pushbutton
UPC	782113469041

Taxonomies, Classifications, and Categories

Category Description	MINATURE PILOT DEVICES.22MM
----------------------	-----------------------------

Packaging

Carton	1
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
Mounting standard	FLUSH Lloyd's Register Certified, IEC 947-5-1 MTTA, UL 508, CSA Certified, CE Marked