



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVRP253PWH Diva 250W Led/Electronic Low Voltage 3WAY White

Lutron

| | |
|------------------|---|
| Catalog Number | DVRP253PWH |
| Manufacturer | Lutron |
| Description | Diva Reverse-Phase Dimmer - Gloss Finish, CFL/Led (Screw-Based), Incandescent/Halogen, Electronic Low-Voltage, 3-Way/Single-Pole, 250W CFL/Led or 500W Inc/Hal/Elv In White |
| Weight per unit | 0.2700 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|---------------|
| actuator | Paddle Switch |
| connection | Wire Leads |
| Connection Type | Wire Leads |
| insulation | Plastic |
| Material | Plastic/Metal |
| Poles | 1 |
| Switch Type | Paddle Switch |
| Voltage Rating | 120 |
| Wattage | 250/500 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|

Descriptions

| | |
|------------------------|---|
| Description | DIVA 250W LED/ELECTRONIC LOW VOLTAGE 3WAY WHITE |
| extra long description | LUT DVRP-253P-WH DIVA 250W LED 500W |
| Long Description | Diva Reverse-phase Dimmer - Gloss Finish, CFL/LED (Screw-based), Incandescent/Halogen, Electronic Low-voltage, 3-way/single-pole, 250W CFL/LED or 500W inc/hal/ELV in white |
| Product Type | Diva 250W Led 500W Elv In White |
| Special Features | Controls 120 V/250 W LED/CFL, and 500 W Inc and ELV loads. Paddle turns on/off. Slide up to brighten, down to dim. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00784276221665 |
| Manufacturers Part Number | DVRP-253P-WH |
| UPC | 784276221665 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Dimmer, reverse-phase, 3-way/single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.27 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | Indoor use only |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA, NOM |