



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50KL36 E50 Operating Lever

*Eaton Corp*

Catalog Number	E50KL36
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Lever, Rotary Lever, Rod Clamp, For 0.12 Inch Diameter Rods, 14-221F(-10-105C), Stainless Steel, UI, Csa, Ce
Weight per unit	0.1500 (lbs/each)
Product Category	Limit Switch Accessories

### Features

actuator	Clamp
dimensions	0.6400 IN X 1.1200 IN X 0.3800 IN

### Descriptions

Description	E50 OPERATING LEVER
extra long description	ETN E50KL36 E50 LS LEVER,ROD CLAMP,
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Lever,Rotary lever,rod clamp,for 0.12 inch diameter rods,14-221F(-10-105C),Stainless Steel,UL,CSA,CE
Product Type	E50 LS Lever, Rod Clamp, 0.12IN Dia Rod

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113138282
Manufacturers Part Number	E50KL36
UPC	782113138282

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch accessory

### Packaging

Carton	1
Weight Per each	0.15



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Industrial Facilities/Factories - Other .....
standard .....	CE,UL Listed,CSA Certified,RoHS Compliant,CE Marked .....