



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57MBL18T111B1 18MM STD Ind Prox 3W DC PNP Mini Conn

Eaton Corp

Catalog Number	E57MBL18T111B1
Manufacturer	Eaton Corp
Description	Inductive Proximity Sensor; Tubular; Shielded; End Sensing Surface; 5 MM (0.20 Inch) Sensing Range; 3-Wire; 10-50 VDC; 18 MM Diameter; Threaded Barrel; 4-Pin Mini Connector; Standard Frequency; N.C. PNP Output
Weight per unit	0.2500 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

dimensions	5.1000 IN X 2.0000 IN X 2.1000 IN
media	Yes

Descriptions

Description	18MM STD IND PROX 3W DC PNP MINI CONN
extra long description	ETN E57MBL18T111B1 18MM STD IND PRO
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Inductive Proximity Sensor; Tubular; Shielded; End Sensing Surface; 5 mm (0.20 inch) Sensing Range; 3-wire; 10-50 VDC; 18 mm Diameter; Threaded Barrel; 4-Pin Mini Connector; Standard Frequency; N.C. PNP Output
Product Type	18MM STD Ind Prox 3W DC PNP Mini Conn

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113427232
Manufacturers Part Number	E57MBL18T111B1
UPC	782113427232

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Packaging

Carton	1
Weight Per each	0.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

standard

UL Listed, CSA Certified, CE Marked