



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E47BMS04 Precision Limit SW Ext Straight Plungr SCRW Term

Eaton Corp

Catalog Number	E47BMS04
Manufacturer	Eaton Corp
Description	Precision Limit Switch, E47, Extended Straight Plunger, Screw Terminals, 15A At 250 Vac, 6A At 30 VDC, 0.01 MM/S-1M/S, 1-SPDT (Form C)
Weight per unit	0.5000 (lbs/each)
Product Category	Miniature & Snap Action Limit

### Features

actuator	Extended straight plunger
connection	Screw Terminal
Contact Configuration	1-SPDT (form C)
Contact Rating	15A at 250 Vac, 6A at 30 Vdc
dimensions	1.9400 IN X 0.6900 IN X 1.3600 IN

### Descriptions

Description	PRECISION LIMIT SW EXT STRAIGHT PLUNGR SCRW TERM
extra long description	ETN E47BMS04 Eaton E47 limit switch
Features	E47 compact prewired limit switches – Eaton's E47 compact prewired limit switches are designed to be a versatile, slim device for hard-to-fit applications where sealing integrity is required. The rugged die-cast aluminum alloy housing, cable connection and switch mechanism are encapsulated for protection against extreme temperature (-10° to 70°C), contaminants, moisture, shock and vibration. E47 precision limit switches – Eaton's E47 precision switches provide high-accuracy switching at an affordable price
Long Description	Precision Limit Switch, E47, Extended straight plunger, Screw Terminals, 15A at 250 Vac, 6A at 30 Vdc, 0.01 mm/s-1m/s, 1-SPDT (Form C)
Product Type	Eaton E47 Limit Switch

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113770888
Manufacturers Part Number	E47BMS04
UPC	782113770888

### Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Limit switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.5

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	UL Listed, CSA Certified