



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E50DS2 E50 Limit Switch Head Side Push Plunger Adjustable

Eaton Corp

Catalog Number	E50DS2
Manufacturer	Eaton Corp
Description	E50 Nema Limit Switch, Head, Side Pushbutton, Adj Spring Ret, 14-250F(-10-121C), Screw Term, Nema 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Diec ZN, UI, Csa, Ce
Weight per unit	0.1100 (lbs/each)
Product Category	Limit Switch Heads

Features

dimensions	1.0500 IN X 1.5400 IN X 2.7900 IN
Material	Die Cast Zinc

Dimensions and Weight

Depth	1.54
Height	2.79
Width	1.54

Descriptions

Description	E50 LIMIT SWITCH HEAD SIDE PUSH PLUNGER ADJUSTABLE
extra long description	ETN E50DS2 E50 LS HEAD,SIDE PUSHBTN
Features	Eaton's E50 modular plug-in limit switches are the industry standard with versatility of design and high reliability for low maintenance, installation and inventory costs. Standard Viton gaskets, seals and boots and a zinc die -cast enclosure provide exceptional chemical resistance to the common coolants, cleansing agents and hydraulic fluids found in machine tool, automotive, wastewater treatment and other heavy-duty industrial applications. Mounting dimensions accommodate both U.S. and DIN standards for
Long Description	E50 NEMA Limit Switch,Head,Side Pushbutton,Adj Spring Ret,14-250F(-10-121C),Screw term,NEMA 1,3,3S,4,4X,6,6P,13,IP67,Diec Zn,UL,CSA,CE
Product Type	E50 LS Head, Side Pushbtn, Adj Spring RTN

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113290638
Manufacturers Part Number	E50DS2
UPC	782113290638

Taxonomies, Classifications, and Categories

Category Description	LIMIT SWITCHES
Type	Heavy duty plug-in limit switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.11

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - Other Stationary Mach Equip In Factory - Machine Tools: Cutting Stationary Mach Equip In Factory - Machine Tools: Forming Ind Facilities & Factories - Industrial Facilities/Factories - Other
Operating Temperature standard	14 CSA Certified,UL Recognized,UL Listed,RoHS Compliant,CE Marked