



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57LBL12A2EA 12MM STD Ind Prox 2W Ac Micro Conn

Eaton Corp

Catalog Number	E57LBL12A2EA
Manufacturer	Eaton Corp
Description	E57 Premium+ Series Tubular Inductive Proximity Sensor, 0.47 Dia, Straight, Sensor Distance: 4 MM, 250 Ma Max Ac, 2 - Wire Ac, NC, 250 Ma At 250VAC, 3 Pin Dual Key Micro Connector, 20-250 Vac Input, < 3% Accuracy, None, Un-Shielded
Weight per unit	1.0 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

dimensions	0.4700 IN X 0.4700 IN X 3.0600 IN
media	Yes

Descriptions

Description	12MM STD IND PROX 2W AC MICRO CONN
extra long description	ETN E57LBL12A2EA 12MM STD IND PROX
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	E57 Premium+ Series Tubular Inductive Proximity Sensor, 0.47 dia, Straight, Sensor distance: 4 mm, 250 mA max AC, 2 - Wire AC, NC, 250 mA at 250Vac, 3 Pin Dual Key Micro Connector, 20-250 Vac input, < 3% accuracy, None, Un-shielded
Product Type	12MM STD Ind Prox 2W Ac Micro Conn

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113743189
Manufacturers Part Number	E57LBL12A2EA
UPC	782113743189

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor

Packaging

Carton	1
Weight Per each	1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

standard

UL Listed, CSA Certified, CE Marked