



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECC04C1ABA Nema 1 C30CNM-Mech Held 12POLE 30a *Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | ECC04C1ABA  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton C30CN Mechanically Held Lighting Contactor, 30 A, 110 V/50 HZ, 120 V/60 HZ, 30 A, Nema 1, Painted Steel, 12-Pole, Mech Held and Mag Latched, C30CN Series, Non-Combination Electrically and Mechanically Held |
| Weight per unit  | 30.0 (lbs/each)   |
| Product Category | Lighting Contactors   |

### Features

|                |                                    |
|----------------|------------------------------------|
| Coil Voltage   | 110-120 Vac, 50/60 Hz              |
| Contact Rating | 30 A                               |
| dimensions     | 7.6200 IN X 6.0000 IN X 12.6000 IN |
| Enclosure Type | Nema 1                             |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | NEMA 1 C30CNM-MECH HELD 12POLE 30A   |
| extra long description | ETN ECC04C1ABA NEMA 1 C30CNM-MECH H  |
| Features               | The C30CN 30A mechanically held lighting contactors are designed for industrial, commercial and outdoor lighting applications where efficient control is required. The mechanically held operation ensures that the contactor will not switch to OFF during control power failure. It also ensures the removal of coil from the circuit for noise-free operation and the elimination of all coil losses after the contactor is latched. The control module microprocessor validates the control signal before operation, so it |
| Long Description       | Eaton C30CN mechanically held lighting contactor, 30 A, 110 V/50 Hz, 120 V/60 Hz, 30 A, NEMA 1, Painted steel, 12-pole, MECH held and MAG latched, C30CN Series, Non-combination electrically and mechanically held  |
| Product Type           | Nema 1 C30CNM-Mech Held 12POLE 30a   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782116157082 |
| Manufacturers Part Number | ECC04C1ABA     |
| UPC                       | 782116157082   |

### Taxonomies, Classifications, and Categories

|                      |                                      |
|----------------------|--------------------------------------|
| Category Description | FREEDOM/NEMA STYLE                   |
| Type                 | Mechanically held lighting contactor |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 30 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsElec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - OtherElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsInd Facilities & Factories - Facility: Lighting and Lighting Controls |
| standard    | UL Listed,cUL Listed   |