

Specifications




Photo is representative

Eaton ECP183608

Eaton Crouse-Hinds series ECP enclosure,
Square cover, 9-11/32" depth, 18" x 36" x 8",
Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP183608
UPC	662276322004
PRODUCT LENGTH/DEPTH	23.66 in
PRODUCT HEIGHT	41.66 in
PRODUCT WIDTH	12.61 in
PRODUCT WEIGHT	355 lb



Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
---------------------	--------------------------------

Product specifications

ENCLOSURE SIZE	18" x 36" x 8"
----------------	----------------

STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1
	Class I, Division 2
	Class II, Division 1
	Class II, Division 2
	Class III
NEMA RATING	3
	3R
	4
	7
	9

COVER TYPE	Square
DEPTH	9-11/32 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP183608 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	IECEX Certificate of Conformity
	Intertek EC-Type Examination Certificate
	ECP Explosionproof Enclosures UL certification
INSTALLATION INSTRUCTIONS	IF 1107 - Mounting Plate Kit
	IF 1639 - ECP Explosionproof Enclosures
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - ECP183608
	ECP Enclosures

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications




Photo is representative

Eaton ECP183608

Eaton Crouse-Hinds series ECP enclosure,
Square cover, 9-11/32" depth, 18" x 36" x 8",
Copper-free aluminum, Tap-in mounting feet

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP183608
UPC	662276322004
PRODUCT LENGTH/DEPTH	23.66 in
PRODUCT HEIGHT	41.66 in
PRODUCT WIDTH	12.61 in
PRODUCT WEIGHT	355 lb



Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
---------------------	--------------------------------

Product specifications

ENCLOSURE SIZE	18" x 36" x 8"
----------------	----------------

STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1
	Class I, Division 2
	Class II, Division 1
	Class II, Division 2
	Class III
NEMA RATING	3
	3R
	4
	7
	9

COVER TYPE	Square
DEPTH	9-11/32 in
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Tap-in mounting feet

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds ECP183608 3D drawing
BROCHURES	Crouse-Hinds series ECP Enclosures Brochure
CATALOGS	Crouse-Hinds series ECP catalog page
CERTIFICATION REPORTS	IECEX Certificate of Conformity
	Intertek EC-Type Examination Certificate
	ECP Explosionproof Enclosures UL certification
INSTALLATION INSTRUCTIONS	IF 1107 - Mounting Plate Kit
	IF 1639 - ECP Explosionproof Enclosures
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - ECP183608
	ECP Enclosures

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

