



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EDCC6 6A 600V Class CC Time Delay Compact Fuse

Edison Fuses

Catalog Number	EDCC6
Manufacturer	Edison Fuses
Description	Eaton Edison Edcc Fuse, Non-Indicating, 6 A, Class CC, 200 Kaic, Standard, 600 V, 300 VDC
Weight per unit	0.0010 (lbs/each)
Product Category	Current Limiting

Features

amperage rating	6 A
amps	6
class	Class CC
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
Fuse Type	Class CC Fuses - Branch Circuits
interrupt rating	200 kAIC
Voltage	600V
Voltage Rating	600 Vac, 300 Vdc

Descriptions

Description	6A 600V CLASS CC TIME DELAY COMPACT FUSE
extra long description	MOR T626-EDCC6 Class CC Fuse - 600V
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Long Description	Eaton Edison EDCC fuse, Non-indicating, 6 A, Class CC, 200 kAIC, Standard, 600 V, 300 Vdc
Product Type	Class CC Fuse - 600V 6a
Special Features	Non-Indicating

Manufacturer Information

Brand	Eaton
GTIN	00782634808190
Manufacturers Part Number	T626-EDCC6
UPC	782634808190



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MIDGET FUSES

Type FUSE

Packaging

Carton 1

Package 10

Weight Per each 0.001

Uses, Certifications, and Standards

Application Datacenters - Facilities: Critical Power

standard CSA Certified,UL Listed,CE Marked,RoHS Compliant