



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ECN1641CAJ FS Combo FVNR SZ 4-ENCL1 480 100A/600 R

Eaton Corp

Catalog Number	ECN1641CAJ
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Enclosed Control , 220V/50 HZ-240V/60 HZ , Nema 1 , Combination Non-Reversing Starter—Circuit Breaker , Hand/Off/Auto Selector Switch , Three-Phase
Weight per unit	90.0 (lbs/each)
Product Category	Nema Combination Starters

Features

Coil Voltage	440V/50 Hz-460V/60 Hz
dimensions	8.4400 IN X 20.5000 IN X 30.5000 IN

Dimensions and Weight

Depth	8.44
Height	30.5
Size	NEMA size 4
Width	20.5

Descriptions

Description	FS COMBO FVNR SZ 4-ENCL1 480 100A/600 R
extra long description	ETN ECN1641CAJ FS COMBO FVNR SZ 4-E
Features	Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor.
Long Description	Eaton Freedom NEMA enclosed control , 220V/50 Hz-240V/60 Hz , NEMA 1 , Combination non-reversing starter—circuit breaker , HAND/OFF/AUTO selector switch , Three-phase
Product Type	FS Combo FVNR SZ 4-ENCL1 480 100A/600 R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114040195
Manufacturers Part Number	ECN1641CAJ
UPC	782114040195

Taxonomies, Classifications, and Categories

Category Description	ENCLOSED
Type	Enclosed control



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	90

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	UL Listed file E1491,Contact Manufacturer