

---

## 42" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP4260-5 | [On-Q](#)



---

### FEATURES & BENEFITS

This standalone hinged door is designed to be purchased in the project trim-out phase to complete installation of the structured wiring assembly.

The door attaches easily to the ENP4280 plastic enclosure without the need for tools or the help of a second installer.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility
- Extra venting along the vertical plane allows for superior heat dissipation
- Doors stack for efficient transportation and warehousing
- Lockable with provided screws
- Covers drywall hole for clean finish
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control

Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 43 mm

Depth (US): 1.68"

Height (Metric): 1105 mm

Height (US): 43.5"

Width (Metric): 406mm

Width (US): 15.97"

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C

---

## 42" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP4260-5 | [On-Q](#)



---

### FEATURES & BENEFITS

This standalone hinged door is designed to be purchased in the project trim-out phase to complete installation of the structured wiring assembly.

The door attaches easily to the ENP4280 plastic enclosure without the need for tools or the help of a second installer.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility
- Extra venting along the vertical plane allows for superior heat dissipation
- Doors stack for efficient transportation and warehousing
- Lockable with provided screws
- Covers drywall hole for clean finish
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control

Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 43 mm

Depth (US): 1.68"

Height (Metric): 1105 mm

Height (US): 43.5"

Width (Metric): 406mm

Width (US): 15.97"

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C