



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EMN25D31GSKM15 3P PB Manual Starter

*Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | EMN25D31GSKM15   |
| Manufacturer     | Crouse-Hinds   |
| Description      | Eaton Crouse-Hinds Series Emn Nema Manual Pushbutton Starter, With Starter, 7.5 HP/10 HP, Square D Starter, Copper-Free Aluminum, Nema Size 1, Three-Pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 Model |
| Weight per unit  | 14.2 (lbs/each)  |
| Product Category | Controls   |

### Features

|                |                         |
|----------------|-------------------------|
| motor power    | 7.5-10 HP               |
| Phase          | 3 Ph                    |
| Poles          | 3                       |
| Voltage Rating | 200-230 Vac/380-575 Vac |

### Dimensions and Weight

|        |                     |
|--------|---------------------|
| Depth  | 7.94                |
| Height | 10.44               |
| Size   | 10.44 x 7.94 x 7.80 |
| Width  | 7.6                 |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 3P PB MANUAL STARTER   |
| extra long description | CRS-H EMN25 D31 GSK M15 MAN STARTER  |
| Features               | Crouse-Hinds series EMN pushbutton style compact manual NEMA starters are used on drilling rigs or mud agitators and shakers where flammable or explosive gases are present. Also used for fans and blowers, pumps, compressors and conveyors. |
| Long Description       | Eaton Crouse-Hinds series EMN NEMA manual pushbutton starter, With starter, 7.5 HP/10 HP, Square D starter, Copper-free aluminum, NEMA size 1, Three-pole, Polyphase, 200-230 Vac/380-575 Vac, Gasket, M15 model                               |
| Product Type           | Man Starter NEMA7 PB 3P Size 1 SQ D GSK  |
| Special Features       | Gasket   |

### Manufacturer Information

|                           |                   |
|---------------------------|-------------------|
| Brand                     | Eaton             |
| GTIN                      | 00662276571143    |
| Manufacturers Part Number | EMN25 D31 GSK M15 |
| UPC                       | 662276571143      |

### Taxonomies, Classifications, and Categories

|                      |                     |
|----------------------|---------------------|
| Category Description | 1PH MANUAL STARTERS |
|----------------------|---------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |         |
|-----------------|---------|
| Carton          | 1       |
| Weight Per each | 14.1699 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Ind Facilities & Factories - Facility: Power Distribution and Control |
| Enclosure                | Cast Aluminum   |
| environmental conditions | where flammable, explosive gases present                              |
| Mounting                 | WALL MOUNT  |
| standard                 | CSA Certified ,UL Listed  |