



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMTELB114X45 1-1/4, 45D Emt Elb

Robroy/Ecn Korns

Catalog Number	EMTELB114X45
Manufacturer	Robroy/Ecn Korns
Description	Elbow, Standard Radius Type; Galvanized Finish; UI 797, Csa C22.2 Approval; Ansi C80.3 Applicable Standard; 25 Per Carton Standard Package; 1-1/4 Inch Trade Size; 1.25 Trade Size In Inch; 1-1/4 Trade Size - Fractional; External Threaded End Type
Weight per unit	1.3 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.3
Bend Angle	45 DEG
Bend Radius	7.25 INCH
End Type	EXTERNAL THREADED
Trade Size - Fractional	1-1/4

Material, Color, and Finish

Finish	Galvanized
--------	------------

Descriptions

Also Known As...	Sweep Elbow Pre-Fab
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	1-1/4,45D EMT ELB
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; ZINC ELECTROPLATED FINISH; UL 797, UL (CANADA AND US), CSA C22.2, CAN/CSA C22.1 APPROVAL; ANSI/NFPA 70, NEC 358, ISO 9001 APPLICABLE STANDARD; 25 PER CARTON STANDARD PACKAGE; 1-1/4 INCH TRADE SIZE; PLAIN END TYPE; 45 DEGREE BEND ANGLE; 7.25 INCH BEND RADIUS; EMTELB MODEL
Long Description	ELBOW, STANDARD RADIUS TYPE; GALVANIZED FINISH; UL 797, CSA C22.2 APPROVAL; ANSI C80.3 APPLICABLE STANDARD; 25 PER CARTON STANDARD PACKAGE; 1-1/4 INCH TRADE SIZE; 1.25 TRADE SIZE IN INCH; 1-1/4 TRADE SIZE - FRACTIONAL; EXTERNAL THREADED END TYPE
Product Type	Elbow

Manufacturer Information

Brand	ECN-KORNS
GTIN	00784011020348
Manufacturers Part Number	EMTELB1-1/4X45
Model	EMTELB
UPC	784011020348



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description EMT ELBOWS

Type STANDARD RADIUS

Trade Size

Trade Size 1-1/4 INCH

Trade Size in inch 1.25

Packaging

Carton 1

Standard Package 25 PER CARTON

Weight Per each 1.26

Uses, Certifications, and Standards

Approval UL 797, CSA C22.2