



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EN4250 42" Enclosure W/Hinged Cover + Lock

*Pass & Seymour/Legrand*

Catalog Number	EN4250
Manufacturer	Pass & Seymour/Legrand
Description	<P>Perfect For Larger Installations, This 42"" Enclosure Features Universal On-Q Style Mounting Holes That Are Compatible With All Bay-Style Modules. It Also Includes Larger Top Openings That Make Pulling Wire Easier As Well As Additional Knockouts, More S
Weight per unit	23.8 (lbs/each)
Product Category	Enclosures & Cabinets

### Features

Cable Entry	(6) rear knockouts
Enclosure Size	42.0
face plate	Hinged Cover and Lock
frame	Cold Rolled Steel
Material	Steel

### Material, Color, and Finish

Color	White
Finish	Powder Coat

### Dimensions and Weight

Depth	3.7"
Height	42.1"
Thickness	0.1
Width	14.3"

### Descriptions

Description	42" ENCLOSURE W/HINGED COVER + LOCK
extra long description	OnQ EN4250 42 ENCL W/HINGED COVER +
Long Description	<p>Perfect for larger installations, this 42"" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s
Product Type	42 Encl W/Hinged Cover + Lock
Special Features	Flanged covers hide drywall openings- Flush and surface-mounted- Mounting tabs provide correct flush-mount position



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428023180
Manufacturers Part Number	EN4250
UPC	804428023180

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	ENCLOSURE

## Packaging

Carton	1
Weight Per each	23.76

## Uses, Certifications, and Standards

Application	Residential
Mounting	Surface or Flush
standard	CSA, CULUS, UL, ROHS, UL (UL985, UL1023, UL1863), cULus, CSA, RoHS