



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F1010GUC 10X10 N1 Uni U-Conn

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | F1010GUC |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Universal U-Connector For Layin Wireway, Fits 10.00X10.00, Gray, Mild Steel |
| Weight per unit | 10.9 (lbs/each) |
| Product Category | Nema Type 1 Wireway & Fittings |

Features

| | |
|-----------|------------|
| ip rating | IP30 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|--------|-----|
| Height | 10 |
| Width | 2.5 |

Descriptions

| | |
|------------------------|---|
| Description | 10X10 N1 UNI U-CONN |
| extra long description | NVENT HOF F1010GUC U-Connector |
| Features | U-Connectors are used to rigidly join fittings to lay-in wireway straight sections. Top swings aside to retain the lay-in feature. One U-connector required at each wireway joint except telescope fittings, panel adapters, open adapters, closure plates or reducers. |
| Long Description | Universal U-Connector for LayIn Wireway, fits 10.00x10.00, Gray, Mild Steel |
| Product Type | U-Connector |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510463908 |
| Manufacturers Part Number | F1010GUC |
| UPC | 783510463908 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | U-Connector |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 5 |
| Weight Per each | 10.85 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | Power Distribution |
| nema rating | 1 Indoor, electrical protection |