



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EV186FBQ 22-18AWG #6STD Red Fork TRML *Panduit Corporation*

| | |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | EV186FBQ |
| Manufacturer | Panduit Corporation |
| Description | Stronghold EV18-6FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 22-18 Awg, Compatible With #6 Stud (M3.5), Are Red In Color, and Come In Packages Of 25. |
| Weight per unit | 0.0700 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|------------|--------|
| connection | Funnel |
| insulation | Vinyl |
| Material | Copper |
| media | Yes |
| Wire Size | #18 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Red |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #6 |
|------|----|

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 22-18AWG #6STD RED FORK TRML |
| extra long description | PAN EV18-6FB-Q StrongHold™ EV18-6FB |
| Long Description | StrongHold EV18-6FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 22-18 AWG, compatible with #6 Stud (M3.5), are red in color, and come in packages of 25. |
| Product Type | Stronghold™ EV18-6FB-Q Loose Piece Forks, Red, Vinyl, 1/8" S |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Panduit® |
| GTIN | 00613056366442 |
| Manufacturers Part Number | EV18-6FB-Q |
| UPC | 613056366442 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 25

Package 250

Weight Per each 0.07

Uses, Certifications, and Standards

Mounting 0.31

standard UL Listed 587H E52164; CSA Certified LR31212