



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F101036RTGV 10X10X36 N3R GLV SC

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | F101036RTGV |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Econotrough Nema Type 3R, 10.00X10.00X36.00, Galvanized, Steel |
| Weight per unit | 39.4 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

Features

| | |
|----------|------------|
| Material | MILD STEEL |
|----------|------------|

Material, Color, and Finish

| | |
|--------|------------|
| Color | Unpainted |
| Finish | Galvanized |

Dimensions and Weight

| | |
|-------|----------------------|
| Depth | 36 |
| Size | 10.00x10.00x36.00 in |
| Width | 10 |

Descriptions

| | |
|------------------------|--|
| Description | 10X10X36 N3R GLV SC |
| extra long description | NVENT HOF F101036RTGV Basic Galvize |
| Features | EconoTrough Galvanized Wiring Trough is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security. |
| Long Description | EconoTrough NEMA Type 3R, 10.00x10.00x36.00, Galvanized, Steel |
| Product Type | Basic Galvized 3R Trough |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510138271 |
| Manufacturers Part Number | F101036RTGV |
| UPC | 783510138271 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Trough |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 39.38 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Power Distribution |
| nema rating | 3R Weather-resistant, except dust |