



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F48T12CWHO 60W T12 48" Cool White High Output 62 Cri R17D

Sylvania-Ledvance

| | |
|------------------|---|
| Catalog Number | F48T12CWHO |
| Manufacturer | Sylvania-Ledvance |
| Description | 60W, 48" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri. |
| Weight per unit | 0.6800 (lbs/each) |
| Product Category | Linear Fluorescent Straight La |

Features

| | |
|---------------------------|-------------------------|
| amperage rating | Ballast Dependent |
| Base | Recessed Double Contact |
| bulb type | T12 |
| Lamp Type | RAPID START |
| lumens | 4,050 |
| Shape | T12 |
| total harmonic distortion | Ballast Dependent |
| Voltage Rating | Ballast Dependent |
| Wattage | 60 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| color rendering index (cri) | 60 |
| color temperature | 4200 |

Descriptions

| | |
|------------------------|---|
| Description | 60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D |
| extra long description | SYL F48T12CWHO/25146 F48T12CWHO 30/ |
| Long Description | 60W, 48" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI. |
| Special Features | COOL WHITE |

Manufacturer Information

| | |
|---------------------------|--------------------|
| Brand | SYLVANIA |
| GTIN | 00046135251467 |
| Manufacturers Part Number | F48T12/CW/HO/25146 |
| UPC | 046135251467 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | Fluorescent |
| Type | FLUORESCENT |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 30 |
| Weight Per each | 0.68 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial/Residential