



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FB0327506ECO 32W T8 22.5" 5K 75CRI 6" Leg Space Is or RS Op

*Sylvania-Ledvance*

|                  |  |
|------------------|--|
| Catalog Number   | FB0327506ECO   |
| Manufacturer     | Sylvania-Ledvance  |
| Description      | 32W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 6" Leg Spacing, 5000K Color Temperature Rare Earth Phosphor, 75 Cri, Suitable For Is or RS Operation, Ecologic |
| Weight per unit  | 0.6200 (lbs/each)  |
| Product Category | Shape Lamps  |

### Features

|                           |                                     |
|---------------------------|-------------------------------------|
| amperage rating           | Ballast Dependent                   |
| average life              | 20000                               |
| Base                      | Medium Bipin                        |
| bulb type                 | T8                                  |
| Lamp Type                 | RS CURVALUME                        |
| lumens                    | 2625 Initial Lumens at 25 Degrees C |
| Shape                     | T8                                  |
| start type                | Rapid Start                         |
| total harmonic distortion | Ballast Dependent                   |
| Voltage Rating            | Ballast Dependent                   |
| Wattage                   | 32                                  |

### Material, Color, and Finish

|                             |                 |
|-----------------------------|-----------------|
| color rendering index (cri) | 75              |
| color temperature           | 5000            |
| Finish                      | Phosphor Coated |

### Dimensions and Weight

|          |   |
|----------|---|
| Diameter | 1 |
|----------|---|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 32W T8 22.5" 5K 75CRI 6" LEG SPACE IS OR RS OP   |
| extra long description | SYL FBO32/750/6/ECO/22053 FBO327506  |
| Long Description       | 32W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 6" leg spacing, 5000K color temperature rare earth phosphor, 75 CRI, suitable for IS or RS operation, ECOLOGIC |
| Product Type           | FBO327506ECO 16/CS 1/Sku   |

### Manufacturer Information

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | SYLVANIA              |
| GTIN                      | 00046135220531        |
| Manufacturers Part Number | FBO32/750/6/ECO/22053 |
| UPC                       | 046135220531          |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 16

Weight Per each ..... 0.62

## Uses, Certifications, and Standards

Application ..... Commercial/Residential