


NEW!
LOW COST!

Low-Cost, Economical Fan/Fixture Box

with Adjustable Steel Bracket and Plastic Box



NEW!

FBR423
Fan/fixture bracket
between joists
in New Construction

Captive
fan/fixture
bracket
installation screws

Arlington's low cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting.

Its steel bracket is fully adjustable to fit between joists spaced 16" to 24".

The box is set for on-center mounting but the 23.0 cubic inch plastic box is positionable anywhere along bracket so you can place the fan or fixture where you want it on the ceiling.

The FBR423 fan/fixture box delivers flush installation on ceilings up to 1-1/4" thick. The bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths, simply bend the bracket ends along the appropriate score line engraved on the product.

- Easy mounting in new construction... fan bracket installation screws ship captive

- UL/CSA Listed

UL rating:

@24" on-center:
70 lb fan; 90 lb fixture

@16" on-center:
70 lb fan; 150 lb fixture

CSA rating: 50 lb fan or fixture




Bracket mounts securely to joists.



Loosen center screw to position box on bracket.



FBR423



Bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths bend the bracket ends along the appropriate score line.

| Catalog Number | UPC/DEI/NAED Mfg. #018997 | Description Fan/Fixture Box | Unit Pkg | Std Pkg |
|----------------|---------------------------|--|----------|---------|
| FBR423 | 52310 | Adjustable steel bracket, 23.0 cu. in. plastic box | 1 | 10 |




Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

NEW!
LOW COST!

Low-Cost, Economical Fan/Fixture Box

with Adjustable Steel Bracket and Plastic Box



NEW!

FBR423
Fan/fixture bracket
between joists
in New Construction

Captive
fan/fixture
bracket
installation screws

Arlington's low cost, economical steel fan/fixture bracket with plastic box delivers super-secure, versatile on-center mounting.

Its steel bracket is fully adjustable to fit between joists spaced 16" to 24".

The box is set for on-center mounting but the 23.0 cubic inch plastic box is positionable anywhere along bracket so you can place the fan or fixture where you want it on the ceiling.

The FBR423 fan/fixture box delivers flush installation on ceilings up to 1-1/4" thick. The bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths, simply bend the bracket ends along the appropriate score line engraved on the product.

- Easy mounting in new construction... fan bracket installation screws ship captive

- UL/CSA Listed

UL rating:

@24" on-center:
70 lb fan; 90 lb fixture

@16" on-center:
70 lb fan; 150 lb fixture

CSA rating: 50 lb fan or fixture




Bracket mounts securely to joists.



Loosen center screw to position box on bracket.



FBR423



Bracket ends are pre-set for a 1/2" ceiling. For other ceiling depths bend the bracket ends along the appropriate score line.

| Catalog Number | UPC/DEI/NAED Mfg. #018997 | Description Fan/Fixture Box | Unit Pkg | Std Pkg |
|----------------|---------------------------|--|----------|---------|
| FBR423 | 52310 | Adjustable steel bracket, 23.0 cu. in. plastic box | 1 | 10 |



Arlington

1 Stauffer Industrial Park
Scranton, PA 18517

800/233.4717

Fax 570/562.0646

www.aifittings.com