

---

## SUPPORT GRIPS STANDARD DUTY, CLOSED MESH

FC100U | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Standard-Duty, Closed mesh, Single Eye Grips. Cable diameter - 1.000-1.240", Bale length - 9", Mesh length - 15", Break strength - 1,680 lbs.

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant tinned-bronze wire.

---

### SPECIFICATIONS

#### GENERAL INFO

Typical Applications: Service Drop

Product Series: Flexcor

Type: Closed Mesh

Duty: Standard Duty

Special Features: Single Eye

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: No

UN SPSC: 39121722

UR: No

#### DIMENSIONS

Weight: 0.24933

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



---

## SUPPORT GRIPS STANDARD DUTY, CLOSED MESH

FC100U | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Standard-Duty, Closed mesh, Single Eye Grips. Cable diameter - 1.000-1.240", Bale length - 9", Mesh length - 15", Break strength - 1,680 lbs.

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant tinned-bronze wire.

---

### SPECIFICATIONS

#### GENERAL INFO

Typical Applications: Service Drop  
Product Series: Flexcor  
Type: Closed Mesh  
Duty: Standard Duty  
Special Features: Single Eye

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: No  
UN SPSC: 39121722  
UR: No

#### DIMENSIONS

Weight: 0.24933

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

