



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FD3090 Type FD BRKR 3P 90A 600VAC Max 18K Aic Eaton Corp

Catalog Number	FD3090
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 90 A, 600 Vac, 250 VDC, Load Side, 50/60 HZ
Weight per unit	4.0 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	90 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
frame	F
media	Yes
Poles	3
Voltage Rating	600 VAC, 250 VDC

### Descriptions

Description	TYPE FD BRKR 3P 90A 600VAC MAX 18K AIC
extra long description	ETN FD3090 TYPE FD BRK 3P 90A 600VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 90 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz
Product Type	Type FD BRK 3P 90A 600VAC Max 18K Aic

### Manufacturer Information

Brand	Eaton
GTIN	00786679305751
Manufacturers Part Number	FD3090
UPC	786679305751

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	UL Listed