



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4300 Danhill Drive
76801-0000, TX Brownwood
Phone: 325-646-6566
Fax: 325-646-3777



FNQR4 4A 600V TD Class CC Fuse *Bussmann Fuses*

Catalog Number	FNQR4
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series FNQ-R Fuse, 4 A, Class CC, Non-Indicating, Ferrule End X Ferrule End, 12 Sec At 200%, 200 Kaic, Melamine Tube, Standard, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	4 A
class	Class CC
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	200 kAIC
Material	Melamine Tube
media	Yes
Voltage Rating	600 V

Descriptions

Description	4A 600V TD CLASS CC FUSE
extra long description	EFSE FNQ-R-4 CLASS CC TIME DELAY
Features	Bussmann's Class CC fuses set the standard in Class CC fuse performance in the industry. Recognized for their superior performance, Bussmann has the right product for your circuit and equipment protection needs. These branch circuit rated, 600v, 200,000a IR fuses offer exceptional protection in the smallest package of any UL class of fuses. Choose from the ultimate protection provided by our Low Peak LP-CC fuses, the time delay of our FNQ-R's for your control transformer and similar control applications or
Long Description	Eaton Bussmann series FNQ-R fuse, 4 A, Class CC, Non-indicating, Ferrule end x ferrule end, 12 sec at 200%, 200 kAIC, Melamine tube, Standard, 600 V
Product Type	Class CC Time Delay
Special Features	Rejection Style

Manufacturer Information

Brand	Eaton
GTIN	00051712147095
Manufacturers Part Number	FNQ-R-4
UPC	051712147095



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4300 Danhill Drive
76801-0000, TX Brownwood
Phone: 325-646-6566
Fax: 325-646-3777

Taxonomies, Classifications, and Categories

Category Description.....MIDGET FUSES

Type.....FUSE

Packaging

Carton.....10

Weight Per each.....0.02

Uses, Certifications, and Standards

Application.....Ind Facilities & Factories - Facility: Safety and Security Systems

standard.....CE Marked,RoHS Compliant