



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## G053C3GN34 3 Pos Sel SWT Long W Contacts

Hubbell--Killark

|                  |   |
|------------------|---|
| Catalog Number   | G053C3GN34  |
| Manufacturer     | Hubbell--Killark  |
| Description      | Killark Go Series Operators Are A Component Use In Conjunction With A Hazardous Location Enclosure to Provide Control Solutions In For; Start/Stop Motor Functions, Led Pilot Light Indications and More. Utilized In Class 1 Division 1 & 2, Class 1 Zone 1 & 2 Areas For Indoor and Outdoor Use. UI Listed and Csa Certified. |
| Weight per unit  | 0.6600 (lbs/each)   |
| Product Category | Selector Switch Complete Assem  |

### Features

|                       |  |
|-----------------------|--|
| action                | Rotary   |
| actuator              | 3 Position Selector Switch   |
| amperage rating       | 10   |
| Contact Configuration | 1-NO/1-NC  |
| Contact Rating        | 0.275A BREAKING @ 250 VDC;0.275A INRUSH @ 250 VDC;0.55A BREAKING @ 125 VDC;0.55A INRUSH @ 125 VDC;1.2A BREAKING @ 600 VAC;1.5A BREAKING @ 480 VAC;10A CARRYING @ 120 VAC;10A CARRYING @ 240 VAC;10A CARRYING @ 480 VAC;10A CARRYING @ 600 VAC;12A INRUSH @ 600 VAC;15A INRUSH @ 480 VAC;2.5A CARRYING @ 125 VDC;2.5A CARRYING @ 250 VDC.;30A INRUSH @ 240 VAC;3A BREAKING @ 240 VAC;60A INRUSH @ 120 VAC;6A BREAKING @ 120 VAC |
| Voltage Rating        | 600 VAC maximum  |

### Dimensions and Weight

|      |                              |
|------|------------------------------|
| Size | 2.25 in x 6.625 in x 1.75 in |
|------|------------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 3 POS SEL SWT LONG W CONTACTS   |
| extra long description | KLRK GO5-3C3G N34 SWITCH, 3POS SEL  |
| Long Description       | Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified. |
| Product Type           | Switch, 3POS Sel Maint 1NO/1NC Long   |
| Special Features       | Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for;START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | KILLARK        |
| GTIN                      | 00783936997216 |
| Manufacturers Part Number | GO5-3C3G N34   |
| series                    | GO             |
| UPC                       | 783936997216   |

## Taxonomies, Classifications, and Categories

|      |                 |
|------|-----------------|
| Type | SELECTOR SWITCH |
|------|-----------------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.66 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures. |
| environmental conditions | Hazardous locations   |
| standard                 | UL, CSA   |