



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FXS51C Exp/PR F/S Switch *Hubbell--Killark*

Catalog Number	FXS51C
Manufacturer	Hubbell--Killark
Description	FXS Series - Factory Sealed Feed-Thru Box and Cover With 1-Pole Tumbler Switch - Conduit Hub Size 3/4 In - 20 Amps
Weight per unit	4.4 (lbs/each)
Product Category	Selector Switch Complete Assem

### Features

action	SP
amperage rating	20
Poles	1
Switch Type	Lever
Voltage Rating	120/277 VAC

### Dimensions and Weight

Size	6.63 in x 6 in x 4.38 in
------	--------------------------

### Descriptions

Description	EXP/PR F/S SWITCH
extra long description	KLRK FXS-51C TUMBL SWITCH 3/4" 1P20
Long Description	FXS Series - Factory Sealed Feed-Thru Box And Cover With 1-Pole Tumbler Switch - Conduit Hub Size 3/4 In - 20 Amps
Product Type	Tumbl Switch 3/4" 1P20A F-Thru
Special Features	Killark SEAL-X Series Factory Sealed Tumbler Switch Controls provide solutions in hazardous location areas to supply;START/STOP Motor Functions and Light Switching. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas where Type 3, 7 & 9 protection ratings are required for indoor and outdoor use. UL Listed and CSA Certified.

### Manufacturer Information

Brand	KILLARK
GTIN	00783936195582
Manufacturers Part Number	FXS-51C
series	FXS
UPC	783936195582

### Taxonomies, Classifications, and Categories

Type	Factory Sealed
------	----------------

### Packaging

Carton	1
Weight Per each	4.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

FXS tumbler switches are suitable for applications where making, breaking, or changing connections in an electrical circuit is required and where conditions of load do not exceed the switch ratings.

Enclosure  
standard

Aluminum factory sealed feed-thru splice box  
UL, CSA