



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## G022GR12D Start Stop Hubbell--Killark

|                  |   |
|------------------|---|
| Catalog Number   | G022GR12D   |
| Manufacturer     | Hubbell--Killark  |
| Description      | Killark Go Series Operators Are A Component Use In Conjunction With A Hazardous Location Enclosure to Provide Control Solutions In For; Start/Stop Motor Functions, Led Pilot Light Indications and More. Utilized In Class 1 Division 1 & 2, Class 1 Zone 1 & 2 Areas For Indoor and Outdoor Use. UI Listed and Csa Certified. |
| Weight per unit  | 0.4000 (lbs/each)   |
| Product Category | Push Button Complete Assemblie  |

### Features

|                       |  |
|-----------------------|--|
| action                | Momentary  |
| actuator              | Double Pushbutton  |
| amperage rating       | 10   |
| Contact Configuration | 1-NO/1-NC  |
| Contact Rating        | 0.275A BREAKING @ 250 VDC;0.275A INRUSH @ 250 VDC;0.55A BREAKING @ 125 VDC;0.55A INRUSH @ 125 VDC;1.2A BREAKING @ 600 VAC;1.5A BREAKING @ 480 VAC;10A CARRYING @ 120 VAC;10A CARRYING @ 240 VAC;10A CARRYING @ 480 VAC;10A CARRYING @ 600 VAC;12A INRUSH @ 600 VAC;15A INRUSH @ 480 VAC;2.5A CARRYING @ 125 VDC;2.5A CARRYING @ 250 VDC.;30A INRUSH @ 240 VAC;3A BREAKING @ 240 VAC;60A INRUSH @ 120 VAC;6A BREAKING @ 120 VAC |
| Voltage Rating        | 600 VAC maximum  |

### Dimensions and Weight

|      |                             |
|------|-----------------------------|
| Size | 6.31 in x 2.25 in x 1.25 in |
|------|-----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | START STOP  |
| extra long description | KLRK GO22-GR12D PUSHBUTTON, DBL SHO   |
| Long Description       | Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for; START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified. |
| Product Type           | Pushbutton, DBL Short Start/Stop  |
| Special Features       | Killark GO SERIES Operators are a component use in conjunction with a Hazardous Location enclosure to provide control solutions in for;START/STOP Motor Functions, LED Pilot Light Indications and more. Utilized in Class 1 Division 1 & 2, Class 1 Zone 1 & 2 areas for indoor and outdoor use. UL Listed and CSA Certified   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | KILLARK        |
| GTIN                      | 00783936222882 |
| Manufacturers Part Number | GO22-GR12D     |
| series                    | GO             |
| UPC                       | 783936222882   |

## Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type                 | Push Button              |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.4 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | G Series custom control panel operators are designed for use in hazardous locations when installed in suitable enclosures such as B7E, EXB, XJB, DB, SWB, and GCS Series boxes and B7, Y7 starter enclosures. |
| environmental conditions | Hazardous locations   |
| standard                 | UL, CSA   |