



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## G2X4LG6 2" X 4" Wire Duct Light Gray *Panduit Corporation*

Catalog Number	G2X4LG6
Manufacturer	Panduit Corporation
Description	The G2X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct Feature A Wide Slot/Finger Design That Provides Greater Sidewall Rigidity and Is Suitable With A Range Of Wire Bundle Sizes. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up to 122°F (50°C). Mounting Holes Provided. 2.0" X 4.0" (50.8 MM X 101.6 MM) and 6' (1.8 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	0.5200 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

### Features

connection	Mounting Holes
Material	PVC
media	Yes

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Length	NA
Size	2.25 x 4.10
Width	2.25

### Descriptions

Description	2" X 4" WIRE DUCT LIGHT GRAY
extra long description	PAN G2X4LG6 Panduct® G2X4LG6 Base W
Long Description	The G2X4LG6 Panduct Lead-Free PVC Wide Slot Wiring Duct feature a wide slot/finger design that provides greater sidewall rigidity and is suitable with a range of wire bundle sizes. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. 2.0" x 4.0" (50.8 mm x 101.6 mm) and 6' (1.8 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® G2X4LG6 Base Wiring Duct

### Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983545858
Manufacturers Part Number	G2X4LG6
UPC	074983545858



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Type ..... Base Wiring Duct .....

## Availability

minimum qty ..... 6 .....

## Packaging

Carton ..... 60 .....

Weight Per foot ..... 0.52 .....

## Uses, Certifications, and Standards

Application ..... Wide slot/finger design provides greater sidewall rigidity and can  
be used in a wide range of applications .....

standard ..... CSA Approved;RoHS Compliant, UL Recognized, CE Compliant .....