



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFRST15GY 15A Comm Self Test GFR Gray

Hubbell Wiring Devices

Catalog Number	GFRST15GY
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Devices, Receptacle, Self Test, Gfci, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

connection	Terminal Screws
Number of Wires	3-Wire Grounding
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	1500;1500.0000
Wire Size	#14 to #12

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	15A COMM SELF TEST GFR GRAY
extra long description	HWDK GFRST15GY 15A COMM SELF TEST G
Features	AUTOGUARD® Self Test Technology 1st introduced by Hubbell over 10 years ago...self test monitoring now required in 2015 UL 943 GFCI Safety Standard... Hubbell AUTOGUARD® GFCI receptacles continually test and monitor for "people protection capability" automatically. This patented safety feature includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost. GFCI auto-monitoring is conducted continuously within every 30 seconds. Also, clear visual indicators are pro
Long Description	Power Protection Devices, Receptacle, Self Test, GFCI, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray
Product Type	15A Comm Self Test GFR Gray
Special Features	Self-Test

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778122026
Manufacturers Part Number	GFRST15GY
UPC	883778122026



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Residential Switches

Packaging

Carton 1

Package 10

Weight Per each 0.35

Uses, Certifications, and Standards

Application Commercial Grade

environmental conditions Indoor Dry unless protected by additional means

Mounting Screw Mount