



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



GL30N38 CMP Lug Cu SHT 3/0 Awg 3/8 BLT-1 SPC

Nsi Industries

Catalog Number	GL30N38
Manufacturer	Nsi Industries
Description	2 Hole Short Barrel Copper Compression Lug W/ Peep Hole 3/0 Awg - 3/8" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	4.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	3/0 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Orange
Finish	Tin Plated

Dimensions and Weight

Size	L=3.11 - W=.900 - OD=.620 - W=.490
------	------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Descriptions

Description	CMP LUG CU SHT 3/0 AWG 3/8 BLT-1 SPC
extra long description	NSI GL30N-38 CMP Lug Cu Sht 3/0 AWG
Features	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 3/0 AWG - 3/8" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 3/0 AWG - 3/8" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu SHT 3/0 Awg 3/8 BLT-1 SPC
Special Features	3/0 AWG (STR) - 3/8 Mounting Hole - 1 Hole Spacing

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381338204
Manufacturers Part Number	GL30N-38
UPC	662381338204

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - Two Hole

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)