



## GLC12HDB Ground Clamp

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | GLC12HDB   |
| Manufacturer     | Nsi Industries   |
| Description      | Nsi GLC-12HDB Heavy Duty Direct Burial Ground Clamps Grip On Pipes Between 1/2" to 1" In Diameter and Are The Ultimate Ground Clamps For Securing Just About Any Size Ground Wire In Just About Any Application. The Bronze Body and Pre-Assembled 304 Stainless Steel Screws Are Made Of Economical, High-Quality Metals That Provide Durable Performance In A Range Of Applications. The Horizontal Lay-In Lug Design Of These Clamps Provides Ultimate Flexibility When Securing Large Conductors and Can Accommodate Wires |
| Weight per unit  | 0.3100 (lbs/each)  |
| Product Category | Ground Rods & Grounding System   |

### Features

|          |             |
|----------|-------------|
| Material | Cast Bronze |
| Warranty | 1 YEAR      |

### Material, Color, and Finish

|                     |                |
|---------------------|----------------|
| Clamp Material      | Cast Bronze    |
| Color               | Bronze         |
| Insulation Color    | Bronze         |
| Insulation Material | Silicon Bronze |

### Dimensions and Weight

|        |       |
|--------|-------|
| Length | 2.362 |
|--------|-------|



## Descriptions

|                        |   |
|------------------------|---|
| Description            | GROUND CLAMP  |
| extra long description | NSI GLC-12HDB Gnd Clamp Lay-In 1/2-   |
| Features               | NSI grounding and bonding products rise to the occasion in a wide variety of indoor and outdoor environments with excellent material quality and flexible designs. These heavy-duty bronze ground clamps with lay-in lugs offer the ultimate solution for grounding large wires in just about any application. Grips onto copper water pipes, tubing, rebar and ground rods using 304 stainless steel screws to tighten the clamp, then grounding conductor is secured in place using a lay-in lug design for ultimate flexibil |
| Long Description       | NSI GLC-12HDB Heavy Duty Direct Burial Ground Clamps grip on pipes between 1/2" to 1" in diameter and are the ultimate ground clamps for securing just about any size ground wire in just about any application. The bronze body and pre-assembled 304 stainless steel screws are made of economical, high-quality metals that provide durable performance in a range of applications. The horizontal lay-in lug design of these clamps provides ultimate flexibility when securing large conductors and can accommodate wires  |
| Product Type           | GND Clamp Lay-In 1/2-1" - Horizontal  |
| Special Features       | UL 486D Listed  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSI            |
| GTIN                      | 00662381005366 |
| Manufacturers Part Number | GLC-12HDB      |
| UPC                       | 662381005366   |

## Taxonomies, Classifications, and Categories

|                      |                                     |
|----------------------|-------------------------------------|
| Category Description | EXOTHERMIC GROUNDING PRODUCTS       |
| Type                 | Heavy Duty Direct Burial Lay-In Lug |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.31 |

## Uses, Certifications, and Standards

|             |                |
|-------------|----------------|
| Application | Grounding Wire |
| standard    | cULus          |