



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GUV3021 3-3-1/2 Ground Clamp

*Abb Installation Products, Inc*

Catalog Number	GUV3021
Manufacturer	Abb Installation Products, Inc
Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 4 - 2/0 Awg, Rod Size 3 to 3-1/2 Inches, Ips Pipe Size Max 3 Inches, Length 5-9/16 Inches, Width 4-13/16 Inches, Depth 1-9/16 Inches
Weight per unit	1.7 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	4 - 2/0
insulation	No

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	5-9/16 in
--------	-----------

### Descriptions

Description	3-3-1/2 GROUND CLAMP
extra long description	ABB GUV3021 U BOLT GRD CLMP 2/0-4 R
Long Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 4 - 2/0 AWG, Rod Size 3 to 3-1/2 Inches, IPS Pipe Size Max 3 Inches, Length 5-9/16 Inches, Width 4-13/16 Inches, Depth 1-9/16 Inches
Product Type	U Bolt GRD CLMP 2/0-4 Rod 3 -3.5
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area

### Manufacturer Information

Brand	Blackburn Grounding
GTIN	00783786803699
Manufacturers Part Number	GUV3021
UPC	783786803699

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GROUND CLAMP



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 10 .....

Weight Per each ..... 1.65 .....

## Uses, Certifications, and Standards

standard ..... UL E3060, CSA 12798 .....