



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## H10091 90 Deg Male L/T Conn, 1", Steel, Ins *Hubbell Wiring Devices*

Catalog Number	H10091
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 1", Steel, Insulated
Weight per unit	0.5500 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

connection	Cap Nut
Material	Iron, Zinc Plated

### Material, Color, and Finish

Color	Metallic
Finish	Metallic

### Dimensions and Weight

Size	1 in
Width	1.719

### Descriptions

Description	90 DEG MALE L/T CONN, 1", STEEL, INS
extra long description	HWDK H10091 90 DEG MALE L/T CONN, 1
Features	Insulated and Non-Insulated Conduit Connectors - Hubbell offers a broad line of metallic liquidtight fittings for use with metallic liq-uidtight conduits and Polytuff I. Hubbell offers trade sizes from 3/8" to 4" in straight, 45°, and 90° body designs. Most connectors are available with either insulated or non-insulated throats. Liquidtight fittings are precision manufactured to exacting standards assuring ease of use and reliability. Straight body 1/2" and 3/4" sizes are listed for UL Type 3R, 4, 12 and 13 envi
Long Description	Kellems Wire Management, Liquidtight System, 90 Degree Male Liquid Tight Connector, 1", Steel, Insulated
Product Type	Metallic Liquidtight Fittings
Special Features	Insulated

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585035444
Manufacturers Part Number	H10091
UPC	783585035444



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Stainless Rigid Conduit
Type	Metallic Liquidtight Fittings

## Packaging

Carton	5
Package	1
Weight Per each	0.55

## Uses, Certifications, and Standards

Application	For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit
environmental conditions	Suitable for use in wet locations when a listed sealing ring is used between box and fitting
Mounting	Between Enclosure and Conduit
nema rating	Suitable for use in hazardous locations per Class 1 Div 2
standard	CSA Certified;UL 514B