



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL1547 Elastogrip Conn, 15A 125V, 5-15R *Hubbell Wiring Devices*

Catalog Number	HBL1547
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Female Connector Body, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.
Weight per unit	0.0780 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Screw Terminals
Current Rating	15
insulation	Insulated Body
Material	COMPOSITE
Number of Conductors	3
pallet quantity	4050
Poles	2-Pole
Voltage Rating	125

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Size	3.00 in x 1.61 in x 3.00 in
------	-----------------------------

Descriptions

Description	ELASTOGRIP CONN, 15A 125V, 5-15R
extra long description	HWDK HBL1547 ELASTOGRIP CONN, 15A 1
Long Description	Straight Blade Devices, Female Connector Body, Elasto-Grip Dust Tight, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.
Product Type	Elastogrip Conn, 15A 125V, 5-15R
Special Features	Dust-Tight

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013039
Manufacturers Part Number	HBL1547
series	Elastogrip
UPC	783585013039



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Connector Body

Packaging

Carton	1
Package	10
Weight Per each	0.078

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15R
standard	CSA Certified to C22.2 No. 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706