



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2735SW LKG WT S/SHRD FL-Inlt, 30A3P 480V, L16-30P *Hubbell Wiring Devices*

Catalog Number	HBL2735SW
Manufacturer	Hubbell Wiring Devices
Description	Watertight Safety-Shroud®, Twist-Lock® Flanged Inlet, 30A 3-Phase Delta 480V Ac, 3-Pole 4-Wire Grounding, Nema L16, Screw Terminal
Weight per unit	0.7000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
insulation	Insulated Body
Number of Wires	4-Wire
pallet quantity	1000
Phase	3
Poles	3-Pole
Voltage Rating	480 V
Wattage	14,400
Wire Size	#16 to #8

Dimensions and Weight

Size	3.75 in x 3.75 in x 2.44 in
------	-----------------------------

Descriptions

Description	LKG WT S/SHRD FL-INLT,30A3P 480V,L16-30P
extra long description	HWDK HBL2735SW LKG WT S/SHRD FL-INL
Long Description	Watertight Safety-Shroud®, Twist-Lock® Flanged Inlet, 30A 3-Phase Delta 480V AC, 3-Pole 4-Wire Grounding, NEMA L16,Screw Terminal
Product Type	LKG WT S/SHRD FL-Inlt, 30A3P 480V, L16-30P
Special Features	Shrouded Watertight Construction

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231969
Manufacturers Part Number	HBL2735SW
UPC	783585231969



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description PLUG FUSES

Type Flanged Inlet

Packaging

Carton 1

Package 5

Weight Per each 0.7

Uses, Certifications, and Standards

Application Extra Heavy Duty Industrial

environmental conditions Watertight

Mounting Screw Mount

nema rating L16-30P

standard UL Listed, CSA Certified To Type 4, 4X And Type 12