



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL5379C FLG-RCPT, 20A 125V, 5-20P, SS *Hubbell Wiring Devices*

Catalog Number	HBL5379C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Weight per unit	0.0910 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	2500
Wire Size	#18 to #12

### Dimensions and Weight

Size	1.71 in x 1.69 in x 1.71 in
------	-----------------------------

### Descriptions

Description	FLG-RCPT, 20A 125V, 5-20P, SS
extra long description	HWDK HBL5379C FLG-RCPT, 20A 125V, 5
Long Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Product Type	FLG-RCPT, 20A 125V, 5-20P, SS
Special Features	Impact resistant thermoplastic construction

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585174457
Manufacturers Part Number	HBL5379C
series	Extra Heavy Duty
UPC	783585174457

### Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Flanged Receptacle



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.091

## Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed, File E2186