



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5969VY Valise Conn, 15A 125V, 5-15R, YI** *Hubbell Wiring Devices*

Catalog Number	HBL5969VY
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.
Weight per unit	0.0510 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	15
connection	Screw Terminals
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
pallet quantity	8400
Poles	2-Pole
Voltage Rating	125

### **Material, Color, and Finish**

Color	Yellow
-------	--------

### **Dimensions and Weight**

Size	2.68 in x 1.32 in x 2.68 in
------	-----------------------------

### **Descriptions**

Description	VALISE CONN, 15A 125V, 5-15R, YL
extra long description	HWDK HBL5969VY VALISE CONN, 15A 125
Long Description	Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 125V, 5-15R, Yellow, Single Pack.
Product Type	Valise Conn, 15A 125V, 5-15R, YI
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585013107
Manufacturers Part Number	HBL5969VY
series	Valise®
UPC	783585013107



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Connector Body

## Packaging

Carton	1
Package	10
Weight Per each	0.051

## Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15R
standard	CSA Certified to C22.2 No. 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706