



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL8300I Dup RCPT, HG, 20A 125V, 5-20R, Iv** *Hubbell Wiring Devices*

Catalog Number	HBL8300I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	5500
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

### **Dimensions and Weight**

Size	3.28 in x 1.65 in x 1.19 in
------	-----------------------------

### **Descriptions**

Description	DUP RCPT, HG, 20A 125V, 5-20R, IV
extra long description	HWDK HBL8300I DUP RCPT, HG, 20A 125
Features	HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these
Long Description	Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Ivory, Single Pack.
Product Type	Dup RCPT, HG, 20A 125V, 5-20R, Iv
Special Features	Self Grounding



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585435725
Manufacturers Part Number	HBL8300I
series	Hospital Grade
UPC	783585435725

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	RECEPTACLE

## Packaging

Carton	10
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Extra Heavy Duty Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186