



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL5366CA Plug Angle, 20A 125V, 5-20P, B/W** *Hubbell Wiring Devices*

Catalog Number	HBL5366CA
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Black and White, Single Pack.
Weight per unit	0.0600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### **Features**

amperage rating	20
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	20
Material	Polycarbonate
Number of Wires	3-Wire
pallet quantity	4500
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	2000
Wire Size	#18 AWG to #10 AWG

### **Dimensions and Weight**

Size	1.21 in x 1.52 in x 2.08 in
------	-----------------------------

### **Descriptions**

Description	PLUG ANGLE, 20A 125V, 5-20P, B/W
extra long description	HWDK HBL5366CA PLUG ANGLE, 20A 125V
Long Description	Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Black and White, Single Pack.
Product Type	Plug Angle, 20A 125V, 5-20P, B/W
Special Features	Weatherproof Boot

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585174006
Manufacturers Part Number	HBL5366CA
series	Insulgrip®
UPC	783585174006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

## Packaging

Carton	1
Package	10
Weight Per each	0.06

## Uses, Certifications, and Standards

Application	Industrial/Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-20P
standard	CSA Certified to C22.2 No. 42 File 280;Fed. Spec. W-C596G;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706