



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HP816P400BS 400A PNL, 1 200A Main Inc *Eaton Corp*

Catalog Number	HP816P400BS
Manufacturer	Eaton Corp
Description	Eaton House Panel, 400A, Aluminum, No Bypass, Nema 3R, Overhead/Underground, 22 Kaic, Lug Landings For Compression, Lugs Not Included, CSR2150, Surface Mounting, C:16, S:1, SP:8, BW/BWH, Ring, Type BR Breakers, 120/240V, 4306, Single-Phase
Weight per unit	118.0 (lbs/each)
Product Category	Residential Meter Socket Circu

Features

amperage rating	400
interrupt rating	10
number of spaces	8
Voltage Rating	120/240 V

Dimensions and Weight

Depth	46
Height	7.75
Width	33

Descriptions

Description	400A PNL, 1 200A MAIN INC
extra long description	ETN HP816P400BS 400A PNL, 1 200A ma
Features	Eaton's House Panel service entrance devices consist of a meter socket and a distribution section. They offer fast, easy and safe installation. Available in CH and BR styles. In addition to residential installations, a house panel can also be used for an apartment, condominium, clubhouse or common area.
Long Description	Eaton house panel, 400A, Aluminum, No bypass, NEMA 3R, Overhead/Underground, 22 kAIC, Lug landings for compression, lugs not included, CSR2150, Surface mounting, C:16, S:1, SP:8, BW/BWH, Ring, Type BR breakers, 120/240V, 4306, Single-phase
Product Type	400A PNL, 1 200A Main Incl and 1 Prov

Manufacturer Information

Brand	Eaton
GTIN	00782114895078
Manufacturers Part Number	HP816P400BS
UPC	782114895078

Taxonomies, Classifications, and Categories

Type	House panel
------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 118

Uses, Certifications, and Standards

Application Residential Bldgs & Facilities - Residential Bldgs & Facilities -
Other

Mounting Surface Mount

standard UL Listed,EUSERC Approved