



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## House Panel

**HPC4046SHLX**

**UPC:**786685376547

### Dimensions:

- **Height:** 8 IN
- **Length:** 31.5 IN
- **Width:** 31.5 IN

**Weight:**123 LB

**Notes:**Load conductors can exit the top, bottom, side or back. Secondary breaker not included.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Bypass:** Lever
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Surface
- **Number Of Circuits:** 6
- **Number Of Sockets:** 1
- **Number Of Spaces:** 4
- **Secondary Circuit Breaker:** BRH/BWH
- **Security:** Ringless
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

**Supporting documents:**



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HPC4046SHLX](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## House Panel

**HPC4046SHLX**

**UPC:**786685376547

### Dimensions:

- **Height:** 8 IN
- **Length:** 31.5 IN
- **Width:** 31.5 IN

**Weight:**123 LB

**Notes:**Load conductors can exit the top, bottom, side or back. Secondary breaker not included.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Bypass:** Lever
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Surface
- **Number Of Circuits:** 6
- **Number Of Sockets:** 1
- **Number Of Spaces:** 4
- **Secondary Circuit Breaker:** BRH/BWH
- **Security:** Ringless
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

**Supporting documents:**



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HPC4046SHLX](#)

**Certifications:**

- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.