



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ICN4S5490C2LSG F54T5HO 120-277V W/Leads

*Advance By Signify*

Catalog Number	ICN4S5490C2LSG
Manufacturer	Advance By Signify
Description	The Right Fit For Your High-Output Applications Programmed Start Operation - Helps to Extend Lamp Life In Frequent Switching Applications Such As Occupancy Sensors or Daylight Harvesting;Starting Capability At -20F - Suited For Cold Temperature Applications (54W Models Only);High-Low Switching - One Ballast Can Easily Switch From 4-Lamp to 2-Lamp Fixtures No Matter What The Conditions Require, Operating At A Variety Of Line Voltages Between 120V to 480V, Whether Located In High Ambient Temperature Environm
Weight per unit	2.0 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

Ballast Factor	1
Lamp Type	T5
Number of Lamps	4
Power Factor	0.98
start type	Programmed Start
total harmonic distortion	10
Voltage Rating	120-277
Wattage	54
Wire Type	SOLID

### Material, Color, and Finish

Housing Material	Metal
------------------	-------

### Dimensions and Weight

Height	4.65
Width	6.69



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	F54T5HO 120-277V W/LEADS
extra long description	ADV 209361 ELE BALLAST (4) F54T5HO
Long Description	The right fit for your high-output applications Programmed Start Operation - Helps to extend lamp life in frequent switching applications such as occupancy sensors or daylight harvesting;Starting Capability at -20F - Suited for cold temperature applications (54W models only);High-Low Switching - One ballast can easily switch from 4-lamp to 2-lamp fixtures No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environm
Product Type	Ele Ballast (4) F54T5HO 120-277V
Special Features	UL, CSA, RoHS

## Manufacturer Information

Brand	Signify Electronics
GTIN	00781087047866
Manufacturers Part Number	209361
UPC	781087047866

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Electronic Fluorescent

## Packaging

Carton	1
Package	6
Weight Per each	2

## Uses, Certifications, and Standards

Frequency Rating	50to60
standard	CSA certificate;UL certificate;CEC Listing;NOM certificate;RoHS Compliant